

X-Cite® illuminators have been qualified for the following microscopes:

Microscope Model	EXFO Adaptor Part Number
ATTO / BD BIOSCIENCE	
Atto Bioscience	810-00034
Atto Bioscience CARV2	810-00036
CARL ZEISS	
AxioExaminer	810-00022
Axiomager	810-00022
AxioObserver	810-00022
AxioScope A1	810-00022
Axiophot	810-00022
Axioplan 1, 2	810-00022
Axioskop 2, 2FS, 40	810-00022 (with external device† use 810-00035)
AxioTech	810-00022
Axiovert 10, 35, 100, 135, S100TV	810-00035
Axiovert 200	810-00022 (with external device† use 810-00035)
Axiovert 400	810-00035
Axiovert 25, 40	810-00037
Discovery.v8 / .v12 / .v20	No adaptor req'd*
LSM	No adaptor req'd*
Stemi SV11	No adaptor req'd*
Stereo Lumar	810-00022
LEICA	
DM2000, DM6000, DMI4000	810-00033
DMIL	810-00033
DMIRB, DMIRM, DMIRE2	810-00033
DMLB	810-00033
DMLFS	810-00033
DMR, DMRXA, DMRXA2	810-00033
MZFLIII, MZ16F, MZ16FA	810-00038
M10, MZ9.5	810-00038
MOTIC	
AE31	810-00055
BA400	810-00055



Microscope Model	EXFO Adaptor Part Number
NIKON	
50i, 80i, 90i	810-00030
AZ100	No adaptor req'd*
Diaphot, Labophot, TMF	810-00030*
E400, E600, E800	810-00030
FN-1	810-00030
SMZ1500, SMZ800	810-00030
TE2000, all other "TE"	810-00030
Ti	810-00030
TS100	810-00030*
For "white light TIRF"	810-00045
most other Nikon microscopes	810-00030
OLYMPUS	
AX70	810-00032
BX series: BX50, BX60	810-00032
BX2 series: BX41, BX51, BX61	810-00032
BX3 series: BX43, BX46, BX53	810-00032
CKX41	810-00032
CK40	810-00032
IX series: IX50, IX70	810-00031
IX2 series: IX51, IX71, IX81	810-00031
MVX10	810-00046
SZX7, 10, 12, 16	810-00032

† External devices include shutters, filter wheels, etc installed between the adaptor and microscope.

* Additional fittings may be required from the microscope manufacturer. Contact EXFO for additional information.

May 20, 2010
MG

